


























TWINMET RETROFIT for cast lip mining excavators of >450 t

Try our robust 3-part tooth system retrofit option and the results will convince you to shift to MTG cast lip or plate lip solutions.

TWINMET Retrofit Range Overview

TOOTH SIZES 2, 4, 6	TOOTH LOCKING		INTERMEDIATE ADAPTER	BOX TYPE	ADAPTER LOCKING		
	PIN	RETAINER ³			SLEEVE	PIN	RETAINER ³
 HEAVY DUTY (EX)	 2MT2P 2MT4P	 2MJ2 STR 2MJ4 STR	 5MJ10-2 / 5MJ30-4 5MJ45-6	 Square Box compatible with Hensley ² and S110 / S130 / S145 noses	 2MT10P-S 2MT30P-S 2MT45P-S	 2MT3P 2MT30P1 2MT5P	 2MJ3 STR 2MJ30 STR 2MJ5 STR
 IMPACT (I)			 2MT30P HD				
 PENETRATION (P)	Or	 2MJ2 STR 2MJ4 STR	 5MJ30-4 ¹	 Octagonal Box⁴ compatible with S130 / S145 ² noses	 2MT30P-S 2MT45P-S	 2MT3P 2MT30P1 2MT5P	 2MJ3 STR 2MJ30 STR 2MJ5 STR
 UNIVERSAL (U)	 2MT4PSE	 5MT30-4-NT	 5MT30-4 / 5MT30-4X 5MT30-6 / 5MT45-6 5MT45-6X		 R30DPN / R45DPN		
 DOUBLE VECTOR (W)							

¹ The retainer needs to be removed from the intermediate adapter, when to be used with the TWINMET retrofit HD locking [2MT30P HD].

² METALOGENIA, S.A. is not the proprietor of the brands identified by an asterisk, and these are mentioned herein solely for the purposes of identifying the destination of the products, there is no existing link between the company and the legitimate proprietors of any such brands.

³ Retainer included in tooth and intermediate adapter but can also be ordered separately.

⁴ Intermediate adapters with octagonal box type are not available in all markets. Please contact our customer service for assistance.